

□□ :

□□□□

□□□□□□

□□□□□□□□

□□□□□□□□

□□

□□□□(V)

□□□□□□□□

2800w□□□□ □□SM52□□

5000□□

□□□□□□□□□□□□

5000□□


□□□□

400V


10000



Visible light spectrum



2. Dimensions Drawing:



- OAL: 740MM
- FL: 690 MM
- CL: 635 MM
- C1: 25MM
- C2: 40MM
- WL: 1000MM

Ceramic Head Drawing:

A*B: 23*11mm



Shenzhen Newplanet Technology Co.,Ltd
 (Shenzhen Suknun Technology Co.,Ltd)
 0086-755-8939 9684(Direct) Fax: 0086-755-28995058
 Email: irlightsales02@hotmail.com

| Machine | Lamp Code | HD part | IR wave | Watt | OL(mm) | Volt (V) | Channel1 (W) | Channel 2 (W) | Line Head | Line 1 | Line 2 | Lamp Style | Use condition | Machine Details |
|---------------------------|-----------------------|--------------------------------|-------------|------|---------|----------|--------------|---------------|-----------|--------|--------|------------|---------------|---|
| SM52 | SM52-SW-A | G4. 170. 0101 | Short | 3300 | 712/740 | 415 | 1650 | 1650 | 23*11 | 300 | 300 | B | Horizontal | Grafix Heidelberg SM52 |
| Heidelberg M | HMO-SW-A | 53. 170. 1311 | Short | 3300 | 740 | 415 | 1650 | 1650 | 23*11 | 500 | 500 | B | Horizontal | Grafix Heidelberg M0 |
| | HMO-MW-B | 53. 170. 1411 | Medium | 1800 | 740 | 415 | 900 | 900 | 33*15 | 500 | 500 | B | Horizontal | Grafix Heidelberg M0 |
| SM72 | SM72-SW-A | 83. 170. 1311 | Short | 3500 | 800 | 415 | 1750 | 1750 | 33*15 | 500 | 500 | B | Horizontal | Grafix Heidelberg 72 |
| | SM72-SW-B | 83. 170. 1411 | Medium | 1900 | 800 | 415 | 950 | 950 | 33*15 | 500 | 500 | B | Horizontal | Grafix Heidelberg 72 |
| SM102-Pre9 | SM102-SW-A | 91. 170. 1311 | Short | 3500 | 1100 | 415 | 3500 | 0 | 23*11 | 500 | 500 | A | Horizontal | Heidelberg SM102(Pre1997) Grafix part: 2130012 |
| | SM102-MW-B | 91. 170. 1411 | Medium | 2500 | 1100 | 415 | 1250 | 1250 | 33*15 | 1000 | 1000 | B | Horizontal | Heidelberg SM102(Pre1997) Grafix part: 2130011 |
| CD74 SM74 MAN500 | SM74-SW-C | M6. 170. 0301 | Short | 6950 | 900 | 400 | 2800 | 2075*2 | 23*11 | 100 | 100 | H | Horizontal | Drystar-Heidelberg SM74/CD74(Post1997) |
| | SM74-FMW-B | | Fast-Medium | 4200 | 820 | 480 | 2100 | 2100 | 33*15 | 500 | 500 | B | Horizontal | Grafix Heidelberg SM74 POST 1997 |
| CD102 SM102 SM105XL | MANGX-FMW-B | | Fast-Medium | 4200 | 820 | 415 | 2100 | 2100 | 33*15 | 500 | 500 | B | Horizontal | Grafix SHS Man Roland 500 |
| | SM102-SW-C | C7. 170. 0301 | Short | 5400 | 1200 | 400 | 3500 | 950*2 | 23*11 | 100 | 100 | H | Horizontal | Drystar |
| SM105XL | SM102-FMW-B B-3000 | | Fast-Medium | 6000 | 1120 | 480 | 3000 | 3000 | 33*15 | 1000 | 1000 | B | Horizontal | Grafix SHS Heidelberg 102 POST 1997 |
| | SM105XL- | F7. 170. 0771 C7. 170. 0716 | Fast-Medium | 6200 | 1160 | 400 | 3100 | 3100 | 33*15 | 500 | 500 | B | Horizontal | Drystar 3000 Heidelberg SM102/CD102/SM102)Post(2004) |
| 907381 | 907381 | 6 | Short | 5400 | 1160 | 400 | 5400 | 0 | 33*15 | 130 | 130 | A | Horizontal | 907381 |
| XL75 | XL75 | L7. 170. 0301 | Short | 3500 | 900 | 400 | 1750 | 1750 | 23*11 | 500 | 500 | B | Horizontal | XL75 |

Twin Lamp Structure:

